

ZCKD17

limit switch head ZCKD - steel ball bearing
mounted roller lever



Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Rotary head
Product compatibility	XCKM XCKL
Associated body	ZCKLD35 ZCKLD31H7 ZCKMD31H7 ZCKLD31 ZCKM6H29 ZCKL7H7 ZCKMD37H29 ZCKM5 ZCKLD39 ZCKM1H7 ZCKLD37 ZCKMD39 ZCKM8 ZCKMD35H29 ZCKL8 ZCKL1H7 ZCKM8H7 ZCKL8H7 ZCKMD37H7 ZCKMD35H7 ZCKM6 ZCKM9 ZCKM5H7 ZCKM1H29 ZCKM8H29 ZCKM7 ZCKMD35 ZCKL1 ZCKM7H29 ZCKM9H29 ZCKLD39H7 ZCKM7H7 ZCKMD31H29 ZCKMD31 ZCKMD39H7 ZCKMD37 ZCKL6H7 ZCKL6 ZCKL5 ZCKM5H29 ZCKLD37H7 ZCKL7 ZCKL5H7 ZCKMD39H29 ZCKM6H7 ZCKM1 ZCKLD35H7
Movement of operating head	Rotary
Type of operator	Roller lever spring return metal (ball bearing mounted)
Type of approach	Lateral approach 2 directions

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22416 - LIMIT SWITCHES,IEC,XCKL
Discount Schedule	T
GTIN	00785901646761
Nbr. of units in pkg.	1
Package weight(Lbs)	0.10000000000000001
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1022 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZCKD17](#)