

# ZCKE645

limit switch head ZCKE - side steel roller  
plunger horizontal - +120 °C

Product availability: Non-Stock - Not normally stocked in distribution facility



ZCK E64

## Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ1H7 ZCKJ11H7 ZCKJ8H29 ZCKJD39H7 ZCKJ2H7 ZCKJ1H29 ZCKJD37H7 ZCKJ8 ZCKJ5H29 ZCKJ1 ZCKJD37H29 ZCKJ11 ZCKJ5 ZCKJ9H29 ZCKJ9H7 ZCKJ6H29 ZCKJ9 ZCKJ8H7 ZCKJ6H7 ZCKJ7H29 ZCKJD31H7 ZCKJD39 ZCKJ2H29 ZCKJ5H7 ZCKJ21 ZCKJD31 ZCKJD35H7 ZCKJD39H29 ZCKJ21H7 ZCKJ6 ZCKJD35H29 ZCKJ7H7 ZCKJD37 ZCKJ11H29 ZCKJ7 ZCKJD35 ZCKJ2 ZCKJD31H29 ZCKJ21H29
Movement of operating head	Linear
Type of operator	Side roller plunger spring return metal (with horizontal roller)
Type of approach	Lateral approach 2 directions

## Complementary

Switch actuation	By 30° cam
Positive opening	With
Product weight	0.45 lb(US) (0.205 kg)
Head material	Metal

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Ambient air temperature for operation	50...248 °F (10...120 °C)
Ambient air temperature for storage	50...248 °F (10...120 °C)
Environmental characteristic	High temperature

## Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	003389110599466
Nbr. of units in pkg.	1
Package weight(Lbs)	0.8000000000000004
Returnability	N
Country of origin	FR

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZCKE645](#)