

Product data sheet

Characteristics

TCSMCN1F10

Modbus shielded cable - M12 female connector
- end with free wires - IP67 - 10 m

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	OsiSense XG
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Accessory / separate part designation	Modbus shielded pre-wired M12 connector
Accessory / separate part destination	Modbus/Uni-Telway network Tap-off box
Cable length	32.81 ft (10 m)

Complementary

Product compatibility	TCSAMT31FP TSXSAC50
Electrical connection	1 female connector M12 straight (A coding) Bare wires
Color	Black
Product weight	1.15 lb(US) (0.52 kg)

Environment

IP degree of protection	IP67
-------------------------	------

Ordering and shipping details

Category	22490 - SENSORS-ULTRASONIC (XX5,6)
Discount Schedule	DS2
GTIN	003389119018517
Nbr. of units in pkg.	1
Package weight(Lbs)	1.28
Returnability	N
Country of origin	PL

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2013
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Wiring Diagram

Modbus Connections



Pin no.		Signal
1	-	Drain (Modbus-SHLD)
2	Red	+ 24 VDC
3	Black	0 V/Modbus-GND
4	White	D0
5	Blue	D1
Connector casing		Shielding

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[TCSMCN1F10](#)