



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Provided equipment	RJ11 Cable User Manual

Physical

Color	Charcoal
Height	2.99 in (7.6 cm)
Width	2.13 in (5.4 cm)
Depth	2.24 in (5.7 cm)
Net Weight	0.18 lb(US) (0.08 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz auto-sensing

Output

Number of power socket outlets	1
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	330
Standards	UL 489 UL 1449
Equipment protection policy	Lifetime : \$25000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Surge Protection and Filtering

Data Lines Protected (multi-line only)	1
NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	40 dB
Peak current	9 kA common mode 4.5 kA normal mode
Surge energy rating	540 J
Data line protection	RJ11 Modem/Fax protection (two wire single line)






Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304218357
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No

Packing Units

Package 1 Height	4.61 in (11.7 cm)
Package 1 width	6.10 in (15.5 cm)
Package 1 Length	2.60 in (6.6 cm)
SCC14	10731304218354
Number of Units in Package 2	12
Package 2 Weight	4.85 lb(US) (2.20 kg)
Package 2 Height	6.75 in (171.45 mm)
Package 2 width	9.75 in (247.65 mm)
Package 2 Length	16.38 in (416.05 mm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P1T](#)