



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Kw Rating	0 W
Rated power in VA	0 VA
Main Output Voltage	120 V
Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Cable length	6 ft (1.83 m)
Number of cables	1

General

Provided equipment	User Manual
--------------------	-------------

Physical

Color	Charcoal
Depth	1.50 in (3.8 cm)
Height	11.50 in (29.2 cm)
Net Weight	0.99 lb(US) (0.45 kg)
Width	2.24 in (5.7 cm)

Input

Input Frequency	50/60 Hz +/- 5 Hz auto-sensing
-----------------	--------------------------------

Output

Max Configurable Power (Watts)	0 W
--------------------------------	-----

Conformance

Product Certifications	CSA
Standards	UL 1449
Equipment protection policy	Lifetime : \$25000

Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Batteries & Runtime

Included Battery Modules	0
Battery Slots Empty	0

Surge Protection and Filtering

Surge energy rating	840 J
---------------------	-------

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304211020
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	PH

Packing Units

Package 1 Height	13.31 in (33.8 cm)
Package 1 width	5.79 in (14.7 cm)
Package 1 Length	1.50 in (3.8 cm)
SCC14	10731304211027
Number of Units in Package 2	12
Package 2 Weight	18.52 lb(US) (8.40 kg)
Package 2 Length	16 in (406.40 mm)
Number of Units in Package 3	288

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P6B](#)