



Overview

| | |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

General

| | |
|--------------------|-------------------------------------|
| Provided equipment | Cat 5 ethernet cable User Manual |
|--------------------|-------------------------------------|

Physical

| | |
|--------------|-----------------------|
| Cable length | 4 ft (1.22 m) |
| Color | Beige |
| Depth | 1.50 in (3.8 cm) |
| Height | 12.99 in (33 cm) |
| Net Weight | 0.79 lb(US) (0.36 kg) |
| Width | 2.01 in (5.1 cm) |

Input

| | |
|---------------------------------|--------------------------------|
| Input power | 1200 W |
| Maximum Line Current per phase | 15 A |
| Input Frequency | 50/60 Hz +/- 5 Hz auto-sensing |
| Plug standard | NEMA 5-15P |
| Maximum Input Current per Phase | 15 A |
| Switching current capacity | 15 A |
| Nominal Input Voltage | 120 V |

Output

| | |
|--------------------------------|------------|
| Number of power socket outlets | 6 |
| Outlet standard | NEMA 5-15R |

Conformance

| | |
|-----------------------------|--------------------|
| UL 1449 TVSS Rating | 400 |
| Product Certifications | ETL |
| Equipment protection policy | Lifetime : \$50000 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company. It is not intended to be used as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environmental

| | |
|---------------------------------------|----------------------------------|
| Ambient air temperature for operation | 32...104 °F (0...40 °C) |
| Relative Humidity | 0...95 % |
| Operating altitude | 0...10000 ft |
| Ambient Air Temperature for Storage | 5...113 °F (-15...45 °C) |
| Storage Relative Humidity | 0...95 % |
| Storage altitude | 0...50000 ft (0.00...15240.00 m) |

Surge Protection and Filtering

| | |
|-----------------------------|--|
| NM Surge Response Time (ns) | 1 ns common mode |
| Common mode rejection | 40 dB |
| Peak current | 72 KA common mode 60 kA per phase normal mode |
| Surge energy rating | 1080 J |
| Data line protection | RJ45 Modem/Fax/DSL/10-100 Base-T protection |

Ordering and shipping details

| | |
|-----------------------|-----------------------------|
| Category | 11309 - APC RESALE PRODUCTS |
| GTIN | 00731304282723 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 1 lb(US) (0.45 kg) |
| Returnability | No |

Packing Units

| | |
|------------------------------|-----------------------|
| Package 1 Height | 14.02 in (35.6 cm) |
| Package 1 width | 4.80 in (12.2 cm) |
| Package 1 Length | 1.81 in (4.6 cm) |
| SCC14 | 10731304282720 |
| Number of Units in Package 2 | 6 |
| Package 2 Weight | 7.35 lb(US) (3.33 kg) |
| Package 2 Height | 4.9 in (124.46 mm) |
| Package 2 width | 11.5 in (292.10 mm) |
| Package 2 Length | 14.9 in (378.46 mm) |
| Number of Units in Package 3 | 810 |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |

Contractual warranty

| | |
|----------|------------------|
| Warranty | Limited Lifetime |
|----------|------------------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P6N](#)