

P6W

APC Essential SurgeArrest 6 Outlet Wall Mount, 120V



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	User Manual Warranty card
--------------------	------------------------------

Physical

Color	Beige
Depth	5.51 in (14 cm)
Height	4.02 in (10.2 cm)
Net Weight	0.44 lb(US) (0.2 kg)
Width	1.50 in (3.8 cm)

Input

Input power	1200 W
Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz auto-sensing
Plug standard	NEMA 5-15P
Maximum Input Current per Phase	15 A
Switching current capacity	15 A
Nominal Input Voltage	120 V

Output

Number of power socket outlets	6
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	400
Product Certifications	ETL
Equipment protection policy	Lifetime : \$50000

Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Surge Protection and Filtering

NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	40 dB
Peak current	72 KA common mode 60 kA per phase normal mode
Surge energy rating	1080 J

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304282730
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No

Packing Units

Package 1 Height	7.76 in (19.7 cm)
Package 1 width	2.24 in (5.7 cm)
Package 1 Length	9.49 in (24.1 cm)
SCC14	10731304282737
Number of Units in Package 2	6
Package 2 Weight	4.58 lb(US) (2.08 kg)
Package 2 Height	10 in (254.00 mm)
Package 2 width	8.4 in (213.36 mm)
Package 2 Length	13.37 in (339.60 mm)
Number of Units in Package 3	504

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P6W](#)