

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Product or component type	Pilot light
Lens type	Fresnel plastic
Light block supply	Via transformer (f = 50/60 Hz) Via integral transformer (f = 50/60 Hz)

Complementary

Bezel material	Plastic
Mounting diameter	1.18 in (30 mm)
Shape of signaling unit head	Round
Cap/operator or lens colour	Green
Light source	Incandescent
Bulb base	BA 9s
[Us] rated supply voltage	220...240 V AC
Operating position	Any position
Operating mode	Normal
CAD overall width	2.13 in (54 mm)
CAD overall height	2.76 in (70 mm)
CAD overall depth	1.65 in (42 mm)
Device presentation	Complete product


Environment

Protective treatment	TC
IP degree of protection	IP66

Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
GTIN	00785901041696
Nbr. of units in pkg.	1
Package weight(Lbs)	0.38
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric:

9001SKP7G31