

Product data sheet

Characteristics

ST181531L10

Probe grounding - 105-130 Vac 50/60Hz rating
- Max load 3 A

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product or component type	Probe
System Voltage	130 V DC

Complementary

Protection type	Overload and short-circuit protection
-----------------	---------------------------------------

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	00785901174103
Nbr. of units in pkg.	1
Package weight(Lbs)	1.4199999999999999
Returnability	N
Country of origin	US

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ST181531L10](#)