



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided Equipment	All required connectors Battery recycling guide Reusable packaging Installation guide
--------------------	--

Physical

Color	Charcoal
Depth	2.52 in (6.4 cm)
Height	7.76 in (19.7 cm)
Net Weight	11.75 lb(US) (5.33 kg)
Width	5.87 in (14.9 cm)

Output

Battery Capacity	7.0 Ah
------------------	--------

Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Operating altitude	0...50000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	32...104 °F (0...40 °C)
Storage altitude	0...10000 ft (0.00...3048.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Placement	Internal Battery
Battery blocks per string	2
Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Enclosed battery cabinet
Battery Voltage	24 V
Battery Type	Lead-Acid battery
RBC Quantity	1

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304219088
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No

Packing Units

Package 1 Height	12.01 in (30.5 cm)
Package 1 width	9.02 in (22.9 cm)
Package 1 Length	4.02 in (10.2 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RBC32](#)