

RBC44

APC Smart-UPS Replacement Battery
Cartridge #44 , 192V, 960VAh, with 2 year
warranty



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Number of cables	1
Battery type	Lead-Acid battery
Provided equipment	All required connectors Battery recycling guide Metallic battery tray or enclosure Reusable packaging Installation guide

Physical

Color	Black
Height	4.80 in (12.2 cm)
Width	7.76 in (19.7 cm)
Depth	23.50 in (59.7 cm)
Net Weight	76.19 lb(US) (34.56 kg)
Mounting Mode	Not rack-mountable
USB compatible	No

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Enclosed battery cartridge
Battery Voltage	192V
Additional information	Each RBC44 consists of 2 battery modules.
RBC Quantity	1

Ordering and shipping details

GTIN	00731304217831
Package weight(Lbs)	82.19 lb(US) (37.28 kg)

Packing Units

Package 1 Height	8.90 in (22.6 cm)
Package 1 width	16.10 in (40.9 cm)
Package 1 Length	30.75 in (78.1 cm)
Number of Units in Package 3	12

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RBC44](#)