

### Complementary

|                       |   |
|-----------------------|---|
| Line Rated Current    | 4 A   |
| AWG gauge             | AWG 22...AWG 14   |
| Depth                 | 6 in (152.40 mm)  |
| Electrical Connection | Screw clamp terminal  |
| Height                | 8 in (203.20 mm)  |
| Permissible voltage   | 600 V AC  |
| Net Weight            | 12 lb(US) (5.44 kg)   |
| Protection Type       | Current protection<br>Harmonic distortion<br>Overvoltage protection |
| Width                 | 8 in (203.20 mm)  |

### Environment

|                        |   |
|------------------------|---|
| Product certifications | CE<br>UL listed file E180243<br>CSA LR29753 |
|------------------------|---|

### Ordering and shipping details

|                       |                                      |
|-----------------------|--------------------------------------|
| Category              | 22062-LINE REACTORS/FILTERS (RL,KLC) |
| Discount Schedule     | CP4C                                 |
| GTIN                  | 785901142645                         |
| Nbr. of units in pkg. | 1                                    |
| Package weight(Lbs)   | 11.00 lb(US) (4.99 kg)               |
| Returnability         | Yes                                  |
| Country of origin     | US                                   |

### Packing Units

|                        |                   |
|------------------------|-------------------|
| Unit Type of Package 1 | PCE               |
| Package 1 Height       | 7.99 in (20.3 cm) |
| Package 1 width        | 7.99 in (20.3 cm) |
| Package 1 Length       | 5.98 in (15.2 cm) |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RL00413](#)