

Complementary

Line Rated Current	12 A
AWG gauge	AWG 22...AWG 5
Depth	6 in (152.40 mm)
Electrical Connection	Screw clamp terminal
Height	8 in (203.20 mm)
Permissible voltage	600 V AC
Net Weight	17 lb(US) (7.71 kg)
Protection Type	Harmonic distortion Overvoltage protection Current protection
Width	8 in (203.20 mm)

Environment

Product certifications	CE UL listed file E180243 CSA LR29753
------------------------	---

Ordering and shipping details

Category	22062-LINE REACTORS/FILTERS (RL,KLC)
Discount Schedule	CP4C
GTIN	785901142669
Nbr. of units in pkg.	1
Package weight(Lbs)	13.00 lb(US) (5.897 kg)
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	7.99 in (20.3 cm)
Package 1 width	7.99 in (20.3 cm)
Package 1 Length	5.98 in (15.2 cm)

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RL01212](#)