

### Complementary

Line Rated Current	25 A
AWG gauge	AWG 22...AWG 5
Depth	5.8 in (147.32 mm)
Electrical Connection	Screw clamp terminal
Height	4.3 in (109.22 mm)
Permissible voltage	600 V AC
Net Weight	20 lb(US) (9.07 kg)
Protection Type	Current protection Overvoltage protection Harmonic distortion
Width	7.2 in (182.88 mm)

### Environment

NEMA Degree of Protection	No enclosure rating (open device)
Product certifications	CSA LR29753 CE UL listed file E180243

### Ordering and shipping details

Category	22062-LINE REACTORS/FILTERS (RL,KLC)
Discount Schedule	CP4C
GTIN	00785901514497
Package weight(Lbs)	20.00 lb(US) (9.072 kg)
Returnability	No
Country of origin	MX

### Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RL02503](#)