

Complementary

Line Rated Current	25 A
AWG gauge	AWG 22...AWG 5
Depth	13.09 in (332.49 mm)
Electrical Connection	Screw clamp terminal
Height	13 in (330.20 mm)
Permissible voltage	600 V AC
Net Weight	32 lb(US) (14.51 kg)
Protection Type	Harmonic distortion Overvoltage protection Current protection
Width	13.22 in (335.79 mm)

Environment

Product certifications	CE CSA LR29753 UL listed file E180243
------------------------	---

Ordering and shipping details

Category	22062-LINE REACTORS/FILTERS (RL,KLC)
Discount Schedule	CP4C
GTIN	00785901142683
Package weight(Lbs)	31.00 lb(US) (14.061 kg)
Returnability	No
Country of origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RL02512](#)