

Complementary

Line Rated Current	200 A
Depth	8.3 in (210.82 mm)
Electrical Connection	Screw clamp terminal
Height	10 in (254.00 mm)
Permissible voltage	600 V AC
Net Weight	100 lb(US) (45.36 kg)
Protection Type	Overvoltage protection Harmonic distortion Current protection
Width	10.8 in (274.32 mm)

Environment

NEMA Degree of Protection	No enclosure rating (open device)
Product certifications	CSA LR29753 UL listed file E180243 CE

Ordering and shipping details

Category	22062-LINE REACTORS/FILTERS (RL,KLC)
Discount Schedule	CP4C
GTIN	00785901536659
Package weight(Lbs)	100.00 lb(US) (45.359 kg)
Returnability	No
Country of origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RL20003](#)