



## Overview

Lead time	Usually in Stock
-----------	------------------



## Main

Kw Rating	2700 W
Rated power in VA	3000 VA
Nb of power socket outlets	2 NEMA L6-20R
Main Output Voltage	208 V
Main Input Voltage	208 V
Plug standard	NEMA L6-20P
Number of rack unit	2U
Cable length	8 ft (2.44 m)
Number of cables	1

## General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Provided equipment	CD with software Documentation CD Rack mounting hardware Rack Mounting support rails Smart UPS signalling RS-232 cable USB cable

## Physical

Mounting Location	Front
Mounting Mode	Rack-mounted
Mounting preference	No preference
Depth	26.89 in (68.3 cm)
Height	3.39 in (8.6 cm)
Net Weight	97.62 lb(US) (44.28 kg)
Width	18.90 in (48 cm)
Two post mountable	0
USB compatible	No

## Input

Efficiency at full load	131...268 V adjustable 141...255 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

## Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	3000 VA
Max Configurable Power (Watts)	2700 W
Transfer Time	4ms typical : 8ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

## Conformance

Equipment protection policy	Lifetime : \$150000
Standards	FCC Part 15 class A UL 1778

## Environmental

Acoustic level	55 dBA
Heat dissipation	348 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

## Batteries & Runtime

Battery Type	Lead-Acid battery
Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	3...5 year(s)
Battery power in VAh	566 VAh runtime
Battery Charge Power (Watts)	188 W rated

## Communications & Management

Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multi-function LCD status and control console
Free slots	1

## Surge Protection and Filtering

Surge energy rating	320 J
---------------------	-------






## Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304279556
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No

## Packing Units

Package 1 Height	10.00 in (25.4 cm)
Package 1 width	23.62 in (60 cm)
Package 1 Length	38.58 in (98 cm)
Number of Units in Package 3	8

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SMT3000RMT2U](#)