



Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually Ships within 3 Weeks

Main

Kw Rating	4000 W
Rated power in VA	5000 VA
Nb of power socket outlets	2 NEMA L6-20R 2 NEMA L6-30R
Main Output Voltage	208 V
Main Input Voltage	208 V
Plug standard	NEMA L6-30P
Number of rack unit	5U
Cable length	8 ft (2.44 m)
Number of cables	1

General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Provided equipment	CD with software Rack Mounting support rails Smart UPS signalling RS-232 cable User Manual Web/SNMP Management Card

Physical

Mounting Location	Front
Mounting Mode	Rack-mounted
Mounting preference	Lower
Depth	25.98 in (66 cm)
Height	8.74 in (22.2 cm)
Net Weight	215.46 lb(US) (97.73 kg)
Width	19.02 in (48.3 cm)
Two post mountable	0
USB compatible	No
Color	Black

Input

Efficiency at full load	131...268 V adjustable 141...255 V
Input Frequency	50/60 Hz +/- 5 Hz manual switch

Output

Harmonic distortion	Less than 5 % at full load
Maximum configurable power in VA	5000 VA
Max Configurable Power (Watts)	4000 W
Transfer Time	2ms typical : 4ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	47...53 Hz for 50 Hz nominal sync to mains 57...63 Hz for 60 Hz nominal sync to mains

Conformance

Product Certifications	CSA
Equipment protection policy	Lifetime : \$150000
Standards	FCC Part 15 class A UL 1778

Environmental

Acoustic level	53 dBA
Heat dissipation	344 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	32...113 °F (0...45 °C)
Ambient Air Temperature for Storage	23...131 °F (-5...55 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Type	Lead-Acid battery
Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	2
Battery life	3...5 year(s)
Battery power in VAh	1632 VAh runtime
Battery Charge Power (Watts)	542 W rated

Communications & Management

Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : and Overload Indicators
Emergency Power Off (EPO)	Optional
Free slots	0
Pre-Installed SmartSlot™ Cards	Network management card

Surge Protection and Filtering

Surge energy rating	480 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No

Packing Units

Package 1 Height	25.00 in (63.5 cm)
Package 1 width	24.02 in (61 cm)
Package 1 Length	30.00 in (76.2 cm)
Number of Units in Package 3	3

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SUA5000RMT5U](#)