



Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial CRN Spacial S3D Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Grey RAL 7030
Fixing mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	2.95 in (75 mm)
Length	78.74 in (2000 mm)
Width	1.97 in (50 mm)
Product weight	1.94 lb(US) (0.88 kg)
Total number of wires	240

Environment

ambient air temperature for operation	23...140 °F (-5...60 °C)
flame retardance	VO conforming to UL 94
fire resistance	1760 °F (960 °C) conforming to IEC 60695-2-1/1
standards	DIN 43659 VDE 0506 VDE 0660

Offer Sustainability

WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
--	--

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AK2GD5075](#)