

GS2GU3N

TeSys GS, disconnect switch, fuse, 3 P, 600 V,
UL 60 A, Type J fuse

Product availability: Stock - Normally stocked in distribution facility



Main

Range	TeSys
Product name	TeSys GS
Device short name	GS2GU
Product or component type	Switch-disconnector-fuse
Device application	Protection
Poles description	3P
Protected poles description	3t
Contacts type and composition	3 NO
[I _{th}] conventional free air thermal current	60 A at 104 °F (40 °C)
[I _e] rated operational current	60 A
Fuse type	UL
Fuse size	J
Network type	AC DC
Network frequency	50/60 Hz

Complementary

Type of operating handle	External frontal
Mounting support	Plate
[U _i] rated insulation voltage	750 V
[U _{imp}] rated impulse withstand voltage	8 kV
Rated operational power in W	55 kW at 690 V 30 kW at 400 V 40 kW at 500 V
Short-circuit withstand	17.6 kA
Mechanical durability	10000 cycles
Electrical durability	6000 cycles
Connections - terminals	Power circuit: lugs-ring terminals cable 0.01...0.02 in ² (6...16 mm ²)
Tightening torque	Power circuit: 30.97 lbf.in (3.5 N.m)

Environment

Standards	UL98 CSA C22.2 No 4
IP degree of protection	IP20 with terminal cover conforming to IEC 60529
Ambient air temperature for operation	-4...158 °F (-20...70 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)
Fire resistance	1760 °F (960 °C) body
Height	5.35 in (136 mm)
Width	5.88 in (149.3 mm)
Depth	4.84 in (123 mm)

Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	00785901547143
Nbr. of units in pkg.	1
Package weight(Lbs)	3.8000000000000003
Returnability	Y
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GS2GU3N](#)