



Main

Range	TeSys
Device short name	GVAP
Product or Component Type	Rotary handle
Accessory / separate part category	Control accessory
Handle colour	Black
Handle front plate colour	Grey
Color	Black Gray

Complementary

Range compatibility	TeSys GV2 TeSys GV3 TeSys U
Rotary handle padlocking	Padlock in OFF position Padlock in ON position
Rotary handle mounting style	Direct
Locking options description	1 to 3 padlocks
Height	1.69 in (43 mm)
Width	2.36 in (60 mm)
Depth	2.36 in (60 mm)
Net Weight	0.33 lb(US) (0.15 kg)

Environment

IP degree of protection	IP54
-------------------------	------

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	3606480160899
Nbr. of units in pkg.	1
Package weight(Lbs)	6.31 oz (179 g)
Returnability	No
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.56 in (6.5 cm)
Package 1 width	3.58 in (9.1 cm)
Package 1 Length	5.31 in (13.5 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	32
Package 2 Weight	13.77 lb(US) (6.245 kg)
Package 2 Height	11.81 in (30 cm)

Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GVAPB54](#)