

Product data sheet

Characteristics

DF3EA50

NFC cartridge fuses, Tesys GS, cylindrical 14 mm x 51 mm, fuse type aM, 400 VAC, 50 A, with striker

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	TeSys fuse-disconnector
Product or component type	Cartridge fuse
Device short name	DF3
System Voltage	400 V AC
Fuse size	14 x 51 mm
Fuse type	NFC
Quantity per set	Set of 10


Complementary

[In] rated current	50 A 400 V
Fuse curve	AM
Local signalling	Striker
Product weight	0.04 lb(US) (0.02 kg)

Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	00785901266617
Nbr. of units in pkg.	10
Package weight(Lbs)	0.01
Returnability	N
Country of origin	TN

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 9848 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[DF3EA50](#)