

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Device short name	XCSL
Enclosure type	Enclosure water resistant indoor/outdoor Enclosure dustproof indoor/outdoor Enclosure ice/sleet proof indoor/outdoor

Complementary

Line Rated Current	10 A
[Us] rated supply voltage	110 V AC
Actuator	Key
Contact operation	Slow-break, break before make
Contacts type and composition	1 NO staggered 2 NC
Depth	1.73 in
Enclosure material	Metal
Height	7.64 in
Installation direction	Front actuator supply Right electromagnet connection
Key locking position	On the left
Locking options description	With locking of actuator, unlocking by key operated lock
Number of poles	3
Permissible voltage	<= 300 V AC
Pilot light	LED orange

Environment

Ambient air temperature for operation	-13...158 °F
IP degree of protection	IP67
NEMA degree of protection	NEMA 1/2/3/4/12
Product certifications	CE UL listed file E164353 CCN NKCR CSA LR4408794 class 3211 03

Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	00785901643210
Nbr. of units in pkg.	1
Package weight(Lbs)	1.2
Returnability	N
Country of origin	FR

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XCSL702F3](#)