

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Device short name	XCSL
Enclosure type	Enclosure water resistant indoor/outdoor Enclosure dustproof indoor/outdoor Enclosure ice/sleet proof indoor/outdoor

Complementary

Line Rated Current	10 A
[Us] rated supply voltage	110 V AC
Actuator	Key
Contact operation	Slow-break, break before make
Contacts type and composition	1 NO staggered 2 NC
Depth	1.73 in
Enclosure material	Metal
Height	7.64 in
Installation direction	Front electromagnet connection Back actuator supply
Key locking position	Front
Locking options description	With locking of actuator, unlocking by key operated lock
Number of poles	3
Permissible voltage	<= 300 V AC
Pilot light	LED orange

Environment

Ambient air temperature for operation	-13...158 °F
IP degree of protection	IP67
NEMA degree of protection	NEMA 1/2/3/4/12

Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	00785901837794
Nbr. of units in pkg.	1
Package weight(Lbs)	1.2
Returnability	N
Country of origin	FR

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XCSL760F3](#)