


Product availability: Stock - Normally stocked in distribution facility



Main

Device short name	XCSTE
Enclosure type	Enclosure corrosion resistance indoor/outdoor Enclosure dust and damp proof indoor/outdoor

Complementary

Line Rated Current	6 A
[Us] rated supply voltage	120 V
Actuator	Key
Contact operation	Slow-break
Contacts type and composition	2 NC
Depth	1.3 in
Electromagnet interlocking	Locking on de-energisation and unlocking on energisation of solenoid
Enclosure material	Plastic
Height	3.67 in
Locking options description	With locking of actuator, unlocking by key operated lock
Number of poles	2
Permissible voltage	<= 300 V AC


Environment

Ambient air temperature for operation	-13...140 °F
IP degree of protection	IP67
NEMA degree of protection	NEMA 4/4X/12

Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	00785901825227
Nbr. of units in pkg.	1
Package weight(Lbs)	1.1000000000000001
Returnability	Y
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1150 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XCSTE7333](#)