



Overview

Model Name	APC Smart-UPS SRT 3000VA RM 120V
Includes	CD with software , Documentation CD , Installation guide , Rack Mounting brackets , Rack Mounting support rails , USB cable , Warranty card
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Output Power Capacity	2700 Watts / 3000 VA
Max Configurable Power (Watts)	2700 Watts / 3000 VA
Nominal Output Voltage	120V
Output Voltage Distortion	Less than 2%
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Crest Factor	3 : 1
Crest Factor	Double Conversion Online
Waveform Type	Sine wave
Output Connections	(1) NEMA L5-30R (Battery Backup) , (8) NEMA 5-20R (Battery Backup)
Bypass	Internal Bypass (Automatic and Manual)

Input

Nominal Input Voltage	120V
Input Frequency	40 - 70 Hz (auto sensing)
Input Connections	NEMA L5-30P
Cord Length	8 feet (2.44 meters)
Maximum Input Current	0 A
Input Breaker Capacity	0 A

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	3 hour(s)
Replacement Battery	APCRBC152
RBC Quantity	1

Communications & Management

Interface Port(s)	RJ-45 Serial , Smart-Slot , USB
Available SmartSlot™ Interface Quantity	1
Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity
Emergency Power Off (EPO)	Yes

Surge Protection and Filtering

Surge energy rating	340 Joules
Filtering	--

Physical

Maximum Height	3.35 inches (85.0 mm)
Maximum Width	17.0 inches (432.0 mm)
Maximum Depth	25.0 inches (635.0 mm)
Rack Height	2 U
Net Weight	69.0 lbs (31.3 kg)
Shipping Weight	88.0 lbs (39.92 kg)
Shipping Height	9.7 inches (246.0 mm)
Shipping Width	23.6 inches (599.0 mm)
Shipping Depth	34.3 inches (871.0 mm)
Master Carton Units	0.0
Master Carton Weight	0.0 lbs
Color	Black
Units per Pallet	6.0

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95% non-condensing %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95% non-condensing %
Storage Elevation	0-50000 feet (0-15000 meters)
Audible noise at 1 meter from surface of unit	55.000 dB
Online Thermal Dissipation	805.000 BTU/hr
Protection Class	IP 20

Conformance

Approvals	CSA C22.2 No.107.3-05 , ENERGY STAR V1.0 (USA) , FCC Part 15 Class A , OSHPD , UL 1778
Standard warranty	3 years repair or replace (excluding battery) and 2 years for battery

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SRT3000RMXLA](#)