

Appliance Outlet, Cord Connector (Rewireable), Straight, for Low Voltage



70° C

**Description**

- Connector:
Screwing cable terminal,
- 1 Function:
Pin temperature 70 °C, Protection class II, Cable
- Note: strain relief has to be ordered separately, mating strain reliefs please find under accessories

References


This type is Phase-out without alternate type
Last order date: 31.12.2012

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [RoHS](#), [CHINA-RoHS](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [CAD-Drawings](#), [Accessories](#), [Detailed request for product](#)

Technical Data

Ratings IEC	7 A / 48 VAC; 50 Hz
Ratings UL/CSA	7 A / 48 VAC; 60 Hz
Dielectric Strength	> 3 kVAC between L-N > 1.5 kVAC between L/N-PE (1 min/50 Hz)
Allowable Operation Temp.	-25 °C to 70 °C
Degree of Protection	from front side IP 20 acc. to IEC 60529
Protection Class	Suitable for appliances with protection class II acc. to IEC 61140
Terminal	Screw clamps
Material: Housing	PA6, black / grey / white, UL 94V-0

Dimensions

Config. Code

1251 - H - A B C 0 - D - E J

The characters are placeholders for the correspondingly keys of selections from the key tables.

1251 - **H** - A B C 0 - D - E J = Type

Type	Configuration key
protection class 2	B

1251 - H - **A** B C 0 - D - E J = Terminals

Terminal L	Configuration key
screw terminal	A

1251 - H - A **B** C 0 - D - E J = Terminals

Terminal N	Configuration key
screw terminal	A

Symbols similar as in table A

1251 - H - A B **C** 0 - D - E J = Terminals

Terminal Ground	Configuration key
without terminal	0

Symbols similar as in table A

1251 - H - A B C 0 - **D** - E J = Color

Color	Configuration key
Black	A
Grey	B
White	D

1251 - H - A B C 0 - D - **E** J = Style

Style	Configuration key
for cord assembly	8

1251 - H - A B C 0 - D - E **J** = Condition

Condition	Configuration key
assembled	1
disassembled	2

Packaging unit 50 Pcs

Accessories

Description



4311.9309
PVC Strain Relief for rewireable connectors



4311.9324
PVC Strain Relief for rewireable connectors

Mating Inlets/Plugs

Category / Description

[Special Connector Designs Overview complete](#)

Appliance inlet for low voltage, Snap-in Mounting, Front Side, Solder or Quick-connect Terminal

[1201](#)

Appliance inlet for low voltage, Snap-in Mounting, Front Side, Solder or Quick-connect Terminal

[1201-A](#)[Special Connector Designs further types to 1251](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schurter:](#)

[4310.0013](#)