

= DURABLE
= RUGGED
= ROBUST



MP-A40 SERIES MOBILE PRINTERS

RELIABLE PRINTING.
SIMPLE OPERATION.
STYLISH DESIGN.

Product Highlights

- Ability to withstand multiple drops from up to **6.6 feet**.
- High-resolution receipts at **4 inch (105mm)** per second.
- **IP54** Rating.
- **MIL-STD-810G** Approved.
- Adjustable to **multiple paper widths** with fixing plater.
- **Bluetooth** or **WiFi** ready



Rugged and Reliable Printing

With the ability to withstand multiple drops from up to 6.6 feet (2 meters), the MP-A40 Series Mobile Printers are known for their highest level print speeds currently available on the market. Imagine being able to print high-resolution receipts at 105 mm per second! What's more is after several tests performed in our product lab, the MP-A40 mobile printer was able to perform at 100% after multiple drops.

Simple Operation, Stylish Design

With up to a 4-inch paper width, and weighing a little more than 1.5 pounds, the MP-A40 Series mobile printers are built tough, but that doesn't mean they lack in style or simplicity. With intuitive drop-in paper setting and easy access button, the printers offer a smart and robust design that fit into the palm of your hand, or belt clip; a small carry-on case offers the option of over-the-shoulder transport.

Technology Options

The MP-A40 Series Mobile Printers offer compatibility with the latest operating systems including Windows, 7, 8, 8.1 and 10. There is also SDK availability for Android, iOS and Windows CE print class libraries for added mobility. The printers also offer auto-detection Bluetooth interface and Wi-Fi capabilities, providing added value and easy transition from cable to wireless communications.

TECHNICAL SPECIFICATIONS

Model	MP-A40 Series Mobile Printer	
Printing	Resolution (dots/mm)	8
	Speed (mm/sec)	105 (4-inch)
Media	Paper Width (mm)	80/100/105/112 *with adjustable paper guide
	Paper Type	Thermal/Thermal Label Paper Roll
	Roll Diameter (mm)	58
Interface	Wire	USB2.0
	Wireless	BT 4.1 (classic) or W-LAN 802.11.a/b/g/n
Command	ESC-POS / CPCL / markup language (HTML)	
Drop ¹	2.0m (6.6 feet) multiple drops	
Operating Temp (C)	-20C (-4F) to +50C (+122F)	
Storage Temp (C)	-30C (-22F) to +70 (+158F)	
IP rating ¹	IP54	
Size (mm)	W156 x D152 x H71	
Weight (g), w/ battery, w/o paper roll	760	
Software	Printer driver, Windows® CE (SDK), Android™ (SDK), iOS (SDK)	
Accessories	AC adapter, Battery, AC cable, USB cable, Single charger, Quad charger, Car charger, Shoulder strap	

*1 Test results under SII conditions



Seiko Instruments U.S.A., Inc.

21221 S. Western Avenue, Suite 250
Torrance, CA 90501
Tel: 310.517.7778
Fax: 310.517.8154
E: printerinfo@seikoinstruments.com
W: www.sii-thermalprinters.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Seiko Instruments:

[MP-A40-WF-00A](#) [MP-A40-BT-00A](#) [MP-A40-B06JK1](#) [MP-A40-W06JK1U](#)