

RAPID PRINT SPEED



MP-B30 SERIES MOBILE PRINTERS

RELIABLE PRINTING.
SIMPLE OPERATION.
STYLISH DESIGN.



Product Highlights

- Ability to withstand multiple drops from up to **6 feet**.
- High-resolution receipts at **5 inch (127mm)** per second.
- **IP54** Rating.
- **NFC** ready for easy-pairing with host device.
- **Bluetooth** or **WiFi** ready
- **Multiple options** for battery charging.



Rugged and Reliable Printing

With the ability to withstand multiple drops from up to 6 feet (1.83 meters), the MP-B30 Series Mobile Printers delivers ruggedness within a compact and lightweight package, unique to the market. Imagine being able to print high-resolution receipts at 127 mm per second! What's more is after several tests performed in our product lab, the MP-B30 mobile printer was able to perform at 100% after multiple drops.

Simple Operation, Stylish Design

With a 3-inch paper width, and weighing a little more than $\frac{3}{4}$ of a pound, the MP-B30 Series mobile printers are built tough, while still being stylish in a compact package. With intuitive drop-in paper setting and easy access button, the printers offer a smart and robust design that fit into your fingertips, or belt clip.

Technology Options

The MP-B30 Series Mobile Printers offer compatibility with the latest operating systems including Windows, 7, 8, 8.1 and 10. Printer drivers for OPOS and POS for .NET are also available. There is also SDK availability for Android, iOS and Windows CE print class libraries for added mobility. The printers also bring new features, with the Bluetooth model offering auto-pairing to a host device via NFC.

TECHNICAL SPECIFICATIONS

Model		MP-B30 Series Mobile Printer
Printing	Resolution (dots/mm)	8
	Speed (mm/sec)	127 (5-inch)
Media	Paper Width (mm)	80
	Paper Type	Thermal Paper Roll
	Roll Diameter (mm)	51
Interface	Wire	
	Wireless	BT 4.1 or W-LAN 802.11.a/b/g/n
Command		ESC-POS™ conformity
Drop ¹		1.8m (6 feet) multiple drops
Operating Temp (C)		-20C (-4F) to +50C (+122F)
Storage Temp (C)		-30C (-22F) to +70 (+158F)
IP rating ¹		IP54
Size (mm)		W105 x D126 x H58
Weight (g), w/ battery, w/o paper roll		395
Software		Printer driver, OPOS, POS for .NET, Windows® CE (SDK), Android™ (SDK), iOS (SDK)
Accessories		AC adapter, Battery, USB cable, Belt clip
Optional Accessories		Charging cradle, Single charger, Quad charger, Car charger



Seiko Instruments U.S.A., Inc.

21221 S. Western Avenue, Suite 250
Torrance, CA 90501
Tel: 310.517.7778
Fax: 310.517.8154
E: printerinfo@seikoinstruments.com
W: www.sii-thermalprinters.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Seiko Instruments:](#)

[MP-B30-W02JK1U-E9](#) [MP-B30-B02JK1-E9](#)