




SERPAC CX28A-YY-A-ZZ


Electronic Enclosures



Enclosure color (YY)


Top-Bottom combinations available

BK=black
CL=clear
TRGY=translucent gray
TRRD=translucent red



Seal color (ZZ)

BK=black
BL=blue
GM=gunmetal
NG=neon green
NO=neon orange
OR=orange
YL=yellow
WH=white



PN	Description
5514A,YY	(1) BW 2C Top,YY
5515A,YY	(1) BW 2C Bottom,YY
5521A,ZZ	(1) CX2 Perimeter Seal, ZZ
6002	(4) #2 X 3/8" PH HD screw TORQUE 35-60 in-oz

Watertight enclosure meets or exceeds:
IP67
NEMA 4X, 12, 13

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SERPAC:

[CX28ABKASBK](#) [CX28ABKASBL](#) [CX28ABKASGM](#) [CX28ABKASNG](#) [CX28ABKASNO](#) [CX28ABKASOR](#)
[CX28ABKASYL](#) [CX28ABKABK](#) [CX28ABKABL](#) [CX28ABKAGM](#) [CX28ABKANG](#) [CX28ABKANO](#) [CX28ABKAOR](#)
[CX28ABKAYL](#) [CX28A-CLBK-A-BK](#) [CX28A-CLBK-A-BL](#) [CX28A-CLBK-A-GM](#) [CX28A-CLBK-A-NG](#) [CX28A-CLBK-A-](#)
[NO](#) [CX28A-CLBK-A-OR](#) [CX28A-CLBK-A-WH](#) [CX28A-CLBK-A-YL](#)