




SERPAC CXL20A-YY-A-ZZ


Electronic Enclosures



Enclosure color (YY)


Top-Bottom combinations available

BK=black
CL=clear
TRGY=translucent gray
TRRD=translucent red



Seal color (ZZ)

BK=black
BL=blue
GM=gunmetal
NG=neon green
NO=neon orange
OR=orange
YL=yellow
WH=white



PN	Description
5510A	(1) BW 2A Top
5511A	(1) BW 2A Bottom
5522A	(1) CXL2 Perimeter Seal
6002	(4) #2 X 3/8" PH HD screw TORQUE 35-60 in-oz

Watertight enclosure meets or exceeds:
IP67
NEMA 4X, 12, 13

ALL DIMENSIONS ARE $\pm .010"$ 9/04/2020
2009 Wright Ave. La Verne, CA 91750
Ph. (626) 331-0517 Fx. (626) 331-8584 serpac.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SERPAC:

[CXL20ABKABK](#) [CXL20ABKAGM](#) [CXL20ABKANG](#) [CXL20ABKABL](#) [CXL20ABKANO](#) [CXL20ABKAOR](#)
[CXL20ABKAYL](#) [CXL20ABKAWH](#) [CXL20A-CLBK-A-BK](#) [CXL20A-CLBK-A-BL](#) [CXL20A-CLBK-A-GM](#) [CXL20A-CLBK-A-](#)
[NG](#) [CXL20A-CLBK-A-NO](#) [CXL20A-CLBK-A-OR](#) [CXL20A-CLBK-A-WH](#) [CXL20A-CLBK-A-YL](#)