




PN	Description	
RB55-X06Y	(1) RB55-X06Y, Top	1
RB55X28Y	(1) RB55X28Y, Bottom	2
8055	(1) RB55 O-Ring	
6051	(4) #6-32 Combo Hd captive Screw	
6022	(4) #10 High/Low Pan Hd x 1/4"	
6113	(4) #6-32 Threaded Insert	


1 = INTERIOR DIMENSIONS (@ BOTTOM)

2 = STANDARD COLORS (Y) ARE: BLACK (B), CLEAR (C) AND GRAY (G)
TOPS AND BOTTOMS ALL POSSIBLE COMBINATIONS AVAILABLE
STANDARD MATERIALS (X) IS: POLYCARBONATE (P)

- Watertight enclosure meets or exceed Nema 4 and or IP67.

DIMENSIONS in Inch
[mm]

ALL DIMENSIONS ARE $\pm .010"$ 8/4/2021
2009 Wright Ave., La Verne, CA. 91750
Ph. (626) 331-0517 Fx. (626) 331-8584 serpac.com



(REFERENCE ONLY)

DIMENSIONS in Inch
[mm]

ALL DIMENSIONS ARE $\pm .010"$ 6/22/2021
2009 Wright Ave, La Verne, Ca. 91750
Ph. (626) 331-0517 Fx. (626) 331-8584 serpac.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SERPAC:

[RB55-A14G10C](#) [RB55-A14G10G](#) [RB55-P14C10C](#) [RB55-P14C10G](#) [RB55-P14C10B](#) [RB55-A14B10C](#) [RB55-P14B10B](#) [RB55-P14B10C](#) [RB55-P14G10G](#) [RB55-P14G10C](#) [RB55-A14C10C](#) [RB55-A14C10G](#) [RB55-A14C10B](#)
[RB55-A14B10B](#)