



## Extra-High Accuracy VOM

Higher accuracy specifications for those more critical measurements are found in the Model 270-5. It has a better than 30% improvement in voltage and resistance accuracy as a full-function/range member of the Simpson 260 type VOM group.

- DCV Accuracy 1.25% of Full Scale
- ACV Accuracy 2% of Full Scale
- Resistance Accuracy 1.0° of Arc
- Diode Protected Self-Shielded Movement
- Includes Batteries and Probe Leads With Alligator Clips

## Specifications

### DC VOLTAGE

Ranges	Accuracy*	Voltage Drop (Nominal)
250mV, 1V, 2.5V, 10V, 50V, 250V, 500V, 1000V	1.25% of full scale @ 77 °F 1.75% of full scale @ 67 °F - 87 °F	20KΩ per volt

### AC VOLTAGE

Ranges	Accuracy*	Voltage Drop (Nominal)
2.5V, 10V, 50V, 250V, 500V, 1000V	2% of full scale @ 77 °F 3% of full scale @ 67 °F - 87 °F	5KΩ per volt

### DECIBEL:

4 Ranges- -20 To +50dB Reference- 0dB=1mW Into 600Ω

### DC CURRENT

Ranges	Accuracy*	Voltage Drop (Nominal)
50μA, 1mA, 10mA, 100mA, 500mA, 10A	0.75% full scale on 50 μA @ 77 °F 1.25% full scale of all others @ 77 °F 1.25% full scale on 50 μA @ 67 °F - 87 °F 1.75% full scale of all others @ 67 °F - 87 °F	250mV on 50 μA and 1mA 255mV on 10mA and 10A 300mV on 100mA 500mV on 500mA

### RESISTANCE

Ranges	Accuracy*	Max. Indication
Rx 1 Rx 100 Rx 10K	1.5° of arc on Rx1 1° of arc on all others	0-2KΩ 0-200KΩ 0-20MΩ

\*Accuracies specified are for the 270-5 in a horizontal position.

## Ordering Information

VOMS	Catalog No.	ACCESSORIES	Catalog No.	ACCESSORIES	Catalog No.
270-5, High Accuracy	12226	Probe Set, Threaded w/Clips	00043	Case, Molded Plastic	45028
270-5RT, High Accuracy, w/ Roll-Top Case	12227	Alligator Clips, Screw On	00425	Case, Yellow Padded Nylon	00832
		150-2 Amp Clamp Adapter, AC	00545	Case, Black Padded Nylon	00834
				Case, Roll-top	00248



## Specifications (Continued)

**BATTERIES:** 1.5V D, 9V (NEDA No. 13F1604A)

**SIZE:** 7"(H) x 5.5"(W) 3.1"(D) (18x14x8cm)

**WEIGHT:** Approximately 3LBS. (1.4Kg)

**FUSE:** F1 1A, 250V, type 3AG, quick acting Littelfuse® Type 312001; F2 2A, 600 Littelfuse® Type BLS or 2A 600V, Bussman® Type BBS.

**CIRCUIT TO GROUND VOLTAGE:** 1000V AC/DC Max

Specifications subject to change without notice.

## "GRAB N GO" PADDED NYLON CASES

Padded Nylon "Grab N Go" made of tough durable nylon enables VOM to be stored for quick field use... test leads remain in panel jacks. Thick padding protects your meter. Available in Yellow (00832) and Black (00834).



## ROLL TOP CASES

Roll-top case made of a durable composite material protects meter during transit/storage. Cover rolls back into case for use. Special storage compartment for test leads under meter.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Simpson:

[12226](#) [12227](#)