

372-3 Ohmmeter

MODEL 372-3 Ohmmeter, 0.2 to 50 MΩ

Provides a wide range of resistance measurements in a small package, .02 ohm to 50 megohms.

Especially useful for checking submersible pumps.

Ideal for use in schools, on test benches or at incoming inspection facilities.

- **Ranges:** 0-500Ω; 0-5KΩ; 0-50KΩ; 0-500KΩ; 0-5 MegΩ and 0-50 MegΩ
- **Top Center Scale:** 5Ω; 50Ω; 500Ω; 5KΩ
- **Bottom Center Scale:** 30KΩ; 300KΩ
- **Accuracy:** ± 3° of Linear Arc Length
- **Includes:** Batteries and Alligator Clip Leads part # 07500



Battery Required:
1.5 "C", NEDA 14A (Qty: 1)
18V Battery Assembly (Qty: 1)

Range	Center (Ohms)	Maximum Current (Zero Ohms)	Maximum Voltage (Open Circuit)
RX 1	5	340 mA	1.5V
RX 10	50	30 mA	1.5V
RX 100	500	3 mA	1.5V
RX 1000	5 K	0.3 mA	1.5V
RX 10K	30 K	0.65 mA	21.5V
RX 100K	300 K	65 μA	21.5V

Ordering Information -	
COMPACT METER	Catalog No.
372-3 Ohmmeter	12311
ACCESSORIES	
Case, Brown Padded Polyester	00836
Leads	07500
18V Battery Assembly	00840

Efficient Customer Service has been a valuable tool for generations of Simpson customers.

Customer Service offers ongoing support for our products and calibration and repair service for all current test equipment.

To obtain service for a discontinued Simpson product, contact Customer Service for assistance.

We offer information regarding our capabilities and referrals to other service centers.

Call (715) 588-3311

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Simpson:

12311 00840