

150-2 AC Amp-Clamp Adapters

Amp-Clamp Adapters

Amp-Clamp current probes, used with analog VOMS provide accurate measurements of high AC current found in power systems and related control circuitry.

The Amp-Clamp jaws are closed over a conductor in the circuit and the current load is indicated on the connected meter.

The 150-2 has six ranges (up to 300 ACA) and is available with banana and reverse banana plugs.



Specifications	
AC Amp-Clamp Adapter	
Model	150-2
Ranges	5A, 10A, 50A, 100A, 250A (on 2.5 VAC Meter Range), 6A, 12A, 30A, 60A, 120A, 300A (on 3 VAC Meter Range)
Accuracy	± 3% Full Scale

PHYSICAL

Dimensions: 7.8" x 3" x 1.1"

Weight: 12 oz.

Max. Cable Dimension: 1.125" diameter

Max. Bus Bar Dimensions: 2.38" x 0.38"

Ordering Information	
Amp-Clamp	Catalog No.
150-2 AC Clamp, VOM Banana Plug	00541
150-2 AC Clamp, VOM Reverse Plug	00545
Cable, replacement, reverse banana (used with 00545)	00529
Cable, replacement, banana (used with 00541)	00533

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Simpson:

[00545](#) [00541](#) [45002](#) [00533](#)