



THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.  
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.  
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE  
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.


DWG. NO.  
JBX1INSFSC

FEMALE INSULATOR, SOLDER CONTACT


| CONTACT LAYOUT  | 02                         | 03      | 04      | 05      |
|-----------------|----------------------------|---------|---------|---------|
| FRONT SIDE VIEW |                            |         |         |         |
| REAR SIDE VIEW  |                            |         |         |         |
| CONTACT         |                            |         |         |         |
| ISO VIEW        |                            |         |         |         |
| CONTACT         | ØC                         | 1.3     | 1.3     | 0.9     |
|                 | ØF                         | 1.1     | 1.1     | 0.8     |
|                 | MAX. AWG                   | 20      | 20      | 24      |
|                 | MAX. CURRENT RATING (A)    | 15      | 15      | 10      |
|                 | CONTACT RESISTANCE (mΩ)    | 3       | 3       | 3.5     |
| INSULATOR       | NUMBER OF CAVITY           | 2       | 3       | 4       |
|                 | MAX. CURRENT RATING        | 15      | 12      | 10      |
|                 | TEST VOLTAGE (Vrms)        | 1600    | 1300    | 1900    |
|                 | WORKING VOLTAGE (Vdc/Vrms) | 760/530 | 600/420 | 900/630 |

CONTACT TYPE : F (FEMALE)  
CONTACT TERMINATION : S (SOLDER)

MATERIAL :  
CONTACT: CUPRO NICKEL  
CLIP: COPPER ALLOY  
INSULATOR: PEEK  
FINISH:  
CONTACTS: GOLD



CATALOG NUMBER DESCRIPTION



|     |                        |                 |                |
|-----|------------------------|-----------------|----------------|
| B   | REVISED PER ECN 12286  | RSK<br>06-10-15 | EV<br>06-10-15 |
| A   | RELEASED PER ECN 12264 | SKV<br>03-10-15 | EV<br>03-10-15 |
| REV | DESCRIPTION            | BY<br>DATE      | CHKD<br>DATE   |

DRAWING TITLE  
JBX, SIZE 1, FEMALE INSULATOR, SOLDER CONTACT  
CAT NO.

JBX1INSFS

CAGE NO: 09922

SIZE: B

CUSTOMER

INTERPRET THIS DRAWING IN ACCORDANCE  
WITH ASME Y14.5M - 1994.

SOURIAU

WWW.SOURIAU.COM

|                   |        |     |          |
|-------------------|--------|-----|----------|
| APPROVAL          | DRAWN: | SKV | 02-02-15 |
|                   | CHKD : | EV  | 02-02-15 |
|                   | DSGN : | EV  | 02-02-15 |
|                   | MFG :  | DH  | 02-02-15 |
|                   | QC :   | BB  | 02-02-15 |
| DRAWING SCALE: NA |        |     |          |
| DRAWING NO.       |        |     | REV      |
| JBX1INSFSC        |        |     | B        |
| 1 OF 2            |        |     |          |

| ORIGIN                                                                                                                                                                               | COUNTRY | JURISDICTION | CLASSIFICATION |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|--------------|----------------|
| X                                                                                                                                                                                    | FR      | Not listed   | N/A            |
|                                                                                                                                                                                      | US      | EAR          | ECCN =EAR99    |
| These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited |         |              |                |

|                                       |               |  |
|---------------------------------------|---------------|--|
| LINEAR MEASURE:                       |               |  |
| THIRD ANGLE PROJECTION                |               |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED |               |  |
| No. OF PLACES                         | mm [INCH]     |  |
| ONE PLACE                             | ±3 [±.1]      |  |
| TWO PLACES                            | ±0.5 [±.02]   |  |
| THREE PLACES                          | ±0.25 [±.010] |  |
| ANGLES±1°                             |               |  |

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.  
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.  
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE  
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.  
JBX11NSFSC

| CONTACT LAYOUT  |                            | 06      | 07      | 08      | 10      | 12      |
|-----------------|----------------------------|---------|---------|---------|---------|---------|
| FRONT SIDE VIEW |                            |         |         |         |         |         |
| REAR SIDE VIEW  |                            |         |         |         |         |         |
| CONTACT         |                            |         |         |         |         |         |
| ISO VIEW        |                            |         |         |         |         |         |
| CONTACT         | ØC                         | 0.7     | 0.7     | 0.7     | 0.5     | 0.5     |
|                 | ØF                         | 0.81    | 0.81    | 0.81    | 0.5     | 0.5     |
|                 | MAX. AWG                   | 22      | 22      | 22      | 28      | 28      |
|                 | MAX. CURRENT RATING (A)    | 7       | 7       | 7       | 5       | 5       |
|                 | CONTACT RESISTANCE (mΩ)    | 5       | 5       | 5       | 10      | 10      |
|                 | NUMBER OF CAVITY           | 6       | 7       | 8       | 10      | 12      |
|                 | MAX. CURRENT RATING        | 7       | 7       | 5       | 2.5     | 2.5     |
|                 | TEST VOLTAGE (Vrms)        | 1400    | 1400    | 1200    | 600     | 500     |
| INSULATOR       | WORKING VOLTAGE (Vdc/Vrms) | 660/460 | 660/460 | 600/420 | 300/200 | 170/120 |

| ORIGIN                                                                                                                                                                               | COUNTRY | JURISDICTION | CLASSIFICATION |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|--------------|----------------|
| X                                                                                                                                                                                    | FR      | Not listed   | N/A            |
|                                                                                                                                                                                      | US      | EAR          | ECCN =EAR99    |
| These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited |         |              |                |

|                                       |               |  |           |
|---------------------------------------|---------------|--|-----------|
| LINEAR MEASURE:                       |               |  | mm (INCH) |
| THIRD ANGLE PROJECTION                |               |  |           |
| TOLERANCES UNLESS OTHERWISE SPECIFIED |               |  |           |
| No. OF PLACES                         | mm [INCH]     |  |           |
| ONE PLACE                             | ±3 [±.1]      |  |           |
| TWO PLACES                            | ±0.5 [±.02]   |  |           |
| THREE PLACES                          | ±0.25 [±.010] |  |           |
| ANGLES ±1°                            |               |  |           |

|                                                                  |                 |                   |          |          |
|------------------------------------------------------------------|-----------------|-------------------|----------|----------|
| DRAWING TITLE                                                    |                 |                   |          |          |
| JBX, SIZE 1, FEMALE INSULATOR, SOLDER CONTACT                    |                 |                   |          |          |
| CAT NO.                                                          |                 |                   |          |          |
| JBX11NSFS                                                        |                 |                   |          |          |
| CAGE NO: 09922                                                   | SIZE: B         |                   | APPROVAL |          |
| CUSTOMER                                                         | SOURIAU         | DRAWN: SKV        |          | 02-02-15 |
|                                                                  |                 | CHKD : EV         |          | 02-02-15 |
|                                                                  |                 | DSGN : EV         |          | 02-02-15 |
|                                                                  |                 | MFG : DH          |          | 02-02-15 |
|                                                                  |                 | QC : BB           |          | 02-02-15 |
| INTERPRET THIS DRAWING IN ACCORDANCE<br>WITH ASME Y14.5M - 1994. | WWW.SOURIAU.COM | DRAWING SCALE: NA |          |          |
|                                                                  |                 | DRAWING NO.       | REV      |          |
|                                                                  |                 | JBX11NSFSC        | B        |          |
|                                                                  |                 |                   | 2 OF 2   |          |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[JBXEA1G05FSSDS](#) [JBXEA1G02FSSDS](#) [JBXEA1G03FSSDS](#) [JBXEA1G04FSSDS](#) [JBXEA1G06FSSDS](#)  
[JBXEA1G07FSSDS](#) [JBXEA1G08FSNDS](#) [JBXEA1G08FSSDS](#)