









THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX0INSMSC

CONTACT LAYOUT		06	07	08
FRONT SIDE VIEW				
REAR SIDE VIEW				
CONTACT				
ISO VIEW				
CONTACT	ØC	0.5	0.5	0.5
	ØF	0.5	0.5	0.5
	MAX. AWG	28	28	28
	MAX. CURRENT RATING (A)	5	5	5
	CONTACT RESISTANCE (mΩ)	10	10	10
	NUMBER OF CAVITY	6	7	8
	MAX. CURRENT RATING	2.5	2.5	2
	TEST VOLTAGE (Vrms)	680	680	680
INSULATOR	WORKING VOLTAGE (Vdc/Vrms)	320/220	320/220	190/130

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:			mm (INCH)
THIRD ANGLE PROJECTION			
TOLERANCES UNLESS OTHERWISE SPECIFIED			
No. OF PLACES	mm [INCH]		
ONE PLACE	±3 [±.1]		
TWO PLACES	±0.5 [±.02]		
THREE PLACES	±0.25 [±.010]		
ANGLES±1°			

DRAWING TITLE						
JBX, SIZE O, MALE INSULATOR, SOLDER CONTACT						
CAT NO.						
JBXOINSMS						
CAGE NO: 09922	SIZE: B		APPROVAL	DRAWN: SKV	02-02-15	
CUSTOMER		SOURIAU		CHKD :	EV	02-02-15
				DSGN :	EV	02-02-15
				MFG :	DH	02-02-15
				QC :	BB	02-02-15
				DRAWING SCALE: NA		
DRAWING NO.				REV		
JBXOINSMSC				B		
2 OF 2						
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.				WWW.SOURIAU.COM		

WWW.SOURIAU.COM

PRO-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[JBXFD0G05MSSDSR](#) [JBXFD0G02MSSDSR](#) [JBXFD0G04MSSDSR](#) [JBXFD0G03MSSDSR](#) [JBXFD0G02MSSDSMR](#)
[JBXFD0G03MSSDSMR](#) [JBXFD0G03MSSDS](#) [JBXFD0G03MSSDSM](#) [JBXFD0G04MSSDSMR](#)
[JBXFD0G04MSNDSMR](#) [JBXFD0G04MSNDSR](#) [JBXFD0G05MSSDS](#) [JBXFD0G05MSSDSMR](#) [JBXFD0G08MSSDSR](#)