



b ; 0 ; RL



ASSEMBLED VIEW


P/N	CONNECTOR SIZE	FLEX SIZE CONDUIT (see note 5)	Ø A Maxi	Ø B ±0.3	C ± 0.6
UTS6FC12XXP/S	12	NW12	30.15	24	61
UTS6FC14XXS	14	NW12	35.1	26.5	61
UTS6FC18XXS	18	NW17	42	35	69.2



MATERIAL :
④ Backshell body :Polyamid
② Seal : Elastomer
③ Retaining clip : Polyamid
⑤ Coupling Nut:Polyamid
Insert:Polyamid
Shell : Polyamid
Coupling spring : stainless steal
O'seal : NBR

PERFORMANCE CHARACTERISTICS :
Operating temperature:-40°C up to 105°C
Corrosion salt spray:500 hours
Sealing in assembly conditions: (with an UTS connector)
-IP68 compliant ; 1 bars/30 min
-IP69K as per DIN40050
Insulation resistance: 5000 M min
Test potential : 2000Vrms for #16 layout
Durability: 250 matings and unmatings
Flammability: Polyamid material classified UL94 V-0

NOTES :
-1-Contact to be ordered separately :refer to UTS catalog
-2-Insert arrangements refer to BT 297 see drawing for information: C142-UTS1-A
-For male plug, only layout size 12
-3-Polarization of connector: refer to :
-UT0-POLARIZATION-C01
-UT0W-POLARIZATION-C01
-4-Delivered as a kit in a plastic bag (individual): with parts 2, 3, 4 and 5
-5-Recommended flexible conduit :PMAFLEX
-6-For assembly instruction, see BT297



P/N : UTS6FC12**P
UTS6FC****S

b	07/06/13	—	Modification notes	22523A
ISS	DATE	Latest modification - by:	J.FEURPRIER	MOD N°
Designed by:	J.FEURPRIER	Date:	02/04/13	CUSTOMER DRAWING
TITLE	ASSEMBLY BACKSHELL AND UTS PLUG CONNECTOR UTS CONNECTOR			
Scale	1/2	General linear Tolerances:	± 0.2	NPRDS / PROJECT IC124509A
SOURIAU	WWW.SOURIAU.COM			This document is the property of SOURIAU It must not be reproduced or communicated without permission
FORMAT	A3	SOURIAU DRG N° C186-UTS1-A		SHEET 1/1

NOT EXPORT CONTROLLED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[UTS6FC128S](#) [UTS6FC128P](#) [UTS6FC1210P](#) [UTS6FC1412S](#) [UTS6FC1210S](#) [UTS6FC1823S](#) [UTS6FC124P](#)
[UTS6FC124S](#) [UTS6FC1832S](#) [UTS6FC1419S](#) [UTS6FC142G1S](#) [UTS6FC147S](#)