

- NOTES:
1. HARDWARE NOT SUPPLIED.
  2. THIS IS A LEAD FREE PRODUCT.
  3. MAX. REFLOW TEMP IS 245°C FOR 5 SEC.

BUSHING FINISH	GOLD	
LEAD FINISH	GOLD	
CAPACITANCE	100pF	+50%/-20%
TEMP. RANGE	-55°C	TD +125°C
CURRENT	5 AMP	
WORKING VOLTAGE	125°C	50 VDC
DC RESISTANCE	.005 Ohms	MAX.

SCHEMATIC

MARKING: NONE

PACKING:

PACK IN BAGS 200 PCS. MAX.


SCI

54F-874-012

LOT NO.

DATE CODE

QTY/BAG

		0	REV. <input type="checkbox"/> 0	TOLERANCES UNLESS OTHERWISE SPECIFIED	
CN 58267-ENG		CHANGE NOTICE		Fractions $\pm 1/64$	<div><p>FAIRVIEW PENNYSYLVANIA</p><p>SPECTRUM CONTROL INC.</p></div>
				Dec. .xx $\pm$	
				Dec. .xxx $\pm$ .010	
				Angles $\pm 0^{\circ} 30'$	
				CODE IDENT. ND. DLSP2	
		DATE 3-16-11	Dwn. KAUFFMAN	Description	54F-874-012
		Ckd.		FT FILTER	
		Scale NONE			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[API Technologies:](#)

[54F-874-012](#)