


NOTES:

1. THIS IS A LEAD FREE PRODUCT.
2. MAX. REFLOW TEMP IS 245°C FOR 5 SEC.

LEAD FINISH: GOLD	
CASING FINISH: GOLD	
CAPACITANCE	500pF +100%-0%
TEMP. RANGE	-55°C TD 125°C
CURRENT	5 AMP MAX.
WORKING VOLTAGE	125°C 200VDC MAX.
D.C. RESISTANCE	.01ohms MAX.

SCHEMATIC



MARKING:

NONE


PACKING:

BAG: SCIF-9925-501

DATE CODE

LOT NO.

QTY./BAG (200 MAX.)

		00		REV. <input type="checkbox"/> Z		TOLERANCES UNLESS OTHERWISE SPECIFIED		<div><p>FAIRVIEW PENNSYLVANIA</p></div> <div>SPECTRUM CONTROL, INC.</div> <div>Dwn. KAUFFMAN</div> <div>Date 3-16-11</div> <div>Apvd.</div> <div>Scale NONE</div> <div>Description</div> <div>FEEDTHRU FILTER</div> <div>SCIF-9925-501</div>	
CN 58267-ENG		CHANGE NOTICE		Fractions $\pm 1/64$		Dec. .xx \pm			
				Dec. .xxx $\pm .005$		Angles $\pm 0^\circ 30'$			
				CODE IDENT. ND.		DLSP2			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[API Technologies:](#)

[SCIF-9925-501](#)