



NOTES:
1. THIS IS A LEAD FREE PRODUCT.
2. MAX. REFLOW TEMP IS 245°C FOR 5 SEC.

LEAD FINISH: GOLD	
CASING FINISH: GOLD	
CAPACITANCE	5000pF +100%/-0%
TEMP. RANGE	-55°C TD 125°C
CURRENT	5 AMP MAX.
WORKING VOLTAGE	125°C 100VDC MAX.
D.C. RESISTANCE	.01ohms MAX.



MARKING:
NONE

PACKING:
BAG: SCIF-9925-502
DATE CODE
LOT NO.
QTY./BAG (200 MAX.)

			0	REV. <input type="checkbox"/> Z	TOLERANCES UNLESS OTHERWISE SPECIFIED	 FAIRVIEW PENNSYLVANIA
CN 58267-ENG			CHANGE NOTICE		Fractions $\pm 1/64$	
					Dec. .xx \pm	
					Dec. .xxx $\pm .005$	
					Angles $\pm 0^{\circ} 30'$	
					CODE IDENT. NO. DLSP2	
					Engr B. DEVINE	Description FEEDTHRU FILTER
					Scale NONE	
						SCIF-9925-502

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[API Technologies:](#)

[SCIF-9925-502](#)