



NOTE:

1. MAXIMUM INSTALLATION TEMP.: 500°F



LEAD FINISH: SILVER	
CAP FINISH: GOLD	
CAPACITANCE	3000pF - 5000pF
TEMP. RANGE	-55°C TO 125°C
CURRENT	15 AMP MAX.
WORKING VOLTAGE	125°C 125 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C	
FREQ. MHz	I.L. (db)
10	5
100	45
1 GHz	70



MARKING:

PART: NONE

BAG: SCI  
859635-1  
LOT #  
DATE CODE  
QTY./BAG (200 MAX)

11

REV. NO.

TOLERANCES UNLESS OTHERWISE SPECIFIED

Fractions  $\pm 1/64$

Dec. .xx $\pm$


Dec. .xxx $\pm$ .010

Angles  $\pm 0^\circ 30'$

CODE IDENT. NO.  
DLSP2

CN 206993  
REDRAWN

CHANGE NOTICE



SPECTRUM CONTROL INC.

Dwn. KRDZALIC

Ckd. 5/14/02

Scale NONE

ERIE, FAIRVIEW  
PENNSYLVANIA

Description

PI FILTER PIN

859635-1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Spectrum Control:](#)

[859635-1](#)