



LEAD FINISH	SOLDER
EYELET FINISH	SOLDER
CAPACITANCE	1750pF MIN.
TEMP. RANGE	-55°C TO +125°C
CURRENT	10 AMPS
WORKING VOLTAGE	85°C: 250 VDC 125°C: 200VDC
I.L. PER MIL-STD-220	
FREQ. MHz	I.L. (db)
10	5
100	50
1 GHz	60



MARKING:
PART: NONE
PACKAGING: TRAY # 27-0040-0031
50 PCS/POCKET
(500/TRAY)
LABEL: 51-707-051
DATE CODE
LOT NO.
QTY/POCKET

- NOTE:
- 1) SUGGESTED MOUNTING HOLE: 0.160
 - 2) SOLDER REFLOW TEMP.: (LEAD) 500°F
(EYELET) 575°F
 - * 3) INCLUDING SOLDER MENISCUS.

	8	7	6	5	4	3	2	1	0	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 SPECTRUM CONTROL INC.	FAIRVIEW PENNSYLVANIA	
	CN 57541-ENG	CN 203570	CN 202689	CN 201259	CN 200023	CN 197458	CN 197164	CN 176359	CN 163400	CHANGE NOTICE	Fractions ± 1/64		Dwn. D.Humphreys	Description
											Dec. .xx±		Date 2-3-11	SOLDER-IN FILTER
											Dec. .xxx± .005		Apvd.	51-707-051
											Angles ±0° 30'		Scale N.T.S.	
											CODE IDENT. NO. OLSP2			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Spectrum Control:](#)

[51-707-051](#)