



NOTES:

- HARDWARE IS INCLUDED.
- PRE-FLATTEN/NOTCH DIMENSIONS ARE:
TOP: .386±.010
BOTTOM: .448±.010

BUSHING FINISH	SILVER
LEAD FINISH	TIN/SILVER
CAPACITANCE	1000pF +100/-0%
TEMP. RANGE	-55°C/+125°C
CURRENT	25 AMPS
WORKING VOLTAGE	125°C 500 VDC
DC RESISTANCE	.01 Ohms MAX.
IL=PER MIL-STD-220	
FREQ. MHz	I.L. (db)
100MHz	15
300MHz	25
1 GHz	35
10 GHz	40
SCHEMATIC	
MARKING:	
PART:	SF102P
BAG:	SCI 54F-806-007
	DATE CODE
	LOT NO.
	QTY/BAG



					00	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 SPECTRUM CONTROL INC.	FAIRVIEW PENNSYLVANIA	
					CN 27663-CPD	CHANGE NOTICE	Fractions ± 1/64		Dwn. P. WELLS	Description
							Dec. .xx±			FLTR., SING., FT, BSHG.
							Dec. .xxx± .010		Date 5-30-06	
							Angles ±0° 30'		Engr. STRUCHEN	
							CODE IDENT. NO. DLSP2	Scale NONE		54F-806-007

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Spectrum Control:](#)

[54F-806-007](#)