



LEAD FINISH: SILVER	
BUSHING FINISH: SILVER	
CAPACITANCE	.050 μ F MIN.
TEMP. RANGE	-55°C TO 125°C
CURRENT	23 10 AMP MAX.
WORKING VOLTAGE	100 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	--
10	36
100	45
1 GHz	60
SCHEMATIC	
MARKING:	
PART: 563	
BAG: 54-790-023	
DATE CODE	
QTY/BAG (200 MAX.)	

NOTES:

1. MAXIMUM MOUNTING TORQUE = 1.5lb-in.
2. HARDWARE IS INCLUDED.

	23	22	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 SPECTRUM CONTROL INC.	ERIE, FAIRVIEW PENNSYLVANIA
				Fractions $\pm 1/64$		
				Dec. .xx \pm		
				Dec. .xxx $\pm .010$		
				Angles $\pm 0^{\circ} 30'$		
	CN 203386	CN 184931	CHANGE NOTICE	CODE IDENT. NO. DLSP2	Dwn. KAUFFMAN Ckd. 8/27/01 Apvd. Scale NONE	Description FEED THRU RESIN SEAL FILTER
						54-790-023

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[API Technologies:](#)

[24-0009-2700](#)