

HOUSING: PBT, GLASS FILLED
UL RATED 94V-0, BLACK.
FRONT SHELL: CARBON STEEL.
BOARDLOCKS AND INSERTS: BRASS
CONTACTS: PHOSPHOR BRONZE






2. FINISH

FRONT SHELL: TIN PLATED.
CONTACTS: GOLD FLASH IN MATING AREA OVER 2.54/m
[.000100] MIN NICKEL ON ENTIRE CONTACT AREA.
TIN PLATING ON SOLDER TAILS.
BOARDLOCKS AND INSERTS: TIN PLATED.

3. ELECTRICAL SPECIFICATIONS:

20-38 OHMS AT 30 MHz TYP.
24-43 OHMS AT 50 MHz TYP.
29-48 OHMS AT 100 MHz TYP.

4v SCI, 56F414-001-HD AND DATE CODE MARKED ON THIS SURFACE.



P.C. BOARD MOUNTING DIMENSIONS

[illegible]



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[API Technologies:](#)

[56F414-001-HD](#)