





DWG. SIZE D	DWG. NO. 031-1648		
REVISIONS			
SYM.	E.C.N.	DATE	APVD.
A	24536	3/12/01	
REVISED SILKSCREEN			



SPECIFICATIONS					
WIRING	INPUT		OUTPUT		
	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD	
				MAX. AMPS	MAX. KVA
SINGLE PHASE	120	50/60	0-140	10	1.4

UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ±					TITLE: SPEC. CONTROL DRAWING VARIABLE TRANSFORMER MODEL: 3PN1010B		 STACO ENERGY PRODUCTS CO. A Components Corporation of Amerstar Company 3511 Cassin Boulevard Dayton, Ohio 45424 USA						
DECIMALS	HOLES	ANGLES	DRAFT	UNITS									
.XX	.0000	.06	1°	IN [mm]									
.XXX	.005												
MATERIAL:		ALL DIMENSIONS APPLY AFTER PLATING			DRAWN BY				DATE	FIRST USED ON	DO NOT SCALE DWG.		
The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.					S.A. SMITH				10/10/96	3PN1010B			
					CHECKER				DATE	WEIGHT APPROX.	CAGE CODE	DWG. SIZE	DWG. NO.
										10.25 LBS	83008		
					ENGINEER				DATE	SCALE	SHEET 1 OF 1		
									1=1			D	031-1648

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Staco:

[3PN1010B](#)