





DWG. SIZE D	DWG. NO. 031-1650		
REVISIONS			
SYM.	E.C.N.	DATE	APVD.
A	24536	3/12/01	
REVISED SILKSCREEN			



SPECIFICATIONS					
WIRING	INPUT		OUTPUT		
	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD	
				MAX. AMPS	MAX. KVA
SINGLE PHASE	120	50/60	0-140	10	1.4

UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ±					UNITS		TITLE: SPEC. CONTROL DRAWING VARIABLE TRANSFORMER MODEL: 3PN1010BA					STACO ENERGY PRODUCTS CO. A Components Corporation of Amerstar Company 3515 Gaucha Boulevard Dayton, Ohio 45423 USA					
DECIMALS	HOLES	ANGLES	DRAFT	IN [mm]													
.XX	.0000	.06	1°	1-1/2°		ALL DIMENSIONS APPLY AFTER PLATING											
MATERIAL:																	
The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.																	
DRAWN BY		DATE		FIRST USED ON		DO NOT SCALE DWG.											
S.A. SMITH		10/10/96		3PN1010BA													
CHECKER		DATE		WEIGHT APPROX.		CAGE CODE		DWG. SIZE		DWG. NO.							
				10.25 LBS		83008		D		031-1650							
ENGINEER		DATE		SCALE		SHEET											
				1=1		1 OF 1											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Staco:

3PN1010BA