





DWG. SIZE D	DWG. NO. 031-5070		
REVISIONS			
SYM.	E.C.N.	DATE	APVD.
A	25144	6/10/03	REVISED & UPDATED
B	25435	8/26/04	UPDATED SILKSCREEN



SPECIFICATIONS					
WIRING	INPUT		OUTPUT		
	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD	
				MAX. AMPS	MAX. KVA
SINGLE PHASE	120	50/60	0-140	22	3.08

UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ±					TITLE:		<div><p>STACO ENERGY PRODUCTS CO. <small>A Components Corporation of Amerasia Company 301 Gassett Boulevard Dayton, Ohio 45403 USA</small></p></div>				
DECIMALS	Holes	ANGLES	DRAFT	UNITS	SPEC. CONTROL DRAWING VARIABLE TRANSFORMER MODEL: 3PN2210B						
XX .0005 .06	.01	1°	1-1/2°	IN [mm]							
MATERIAL:											
ALL DIMENSIONS APPLY AFTER PLATING					DRAWN BY		DATE	FIRST USED ON	DO NOT SCALE. DWG.		
The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.					S.A. SMITH		5/22/96	3PN2210B			
					CHECKER	DATE	WEIGHT APPROX.	CAGE CODE	DWG. SIZE	DWG. NO.	
							24 LBS	83008			
					ENGINEER	DATE	SCALE	SHEET		D	031-5070
							1=1	1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Staco:

[3PN2210B](#)