


# **AVERY DENNISON MARKETING SPECIFICATION**

THE SUBJECT MATTER DISCLOSED HEREIN EMBODIES PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF THE AVERY DENNISON CO. NONE OF WHICH SHALL BE COPIED, REPRODUCED, DISCLOSED TO OTHERS, PUBLISHED OR USED IN WHOLE OR IN PART, FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS BEING MADE AVAILABLE WITHOUT THE EXPRESS ADVANCE WRITTEN PERMISSION OF A DULY AUTHORIZED AGENT OF THE COMPANY. THIS DOCUMENT IS THE PROPERTY OF THE AVERY DENNISON CO. AND IS TO BE RETURNED TO THE COMPANY ON DEMAND.

## **HISTORY**

REV.	DATE	DESCRIPTION
C	2NOV12	UPDATED FILE FORMAT & MATCH PRINT TO PART



MOUNTING:	M6 STUD
TENSILE STRENGTH:	50 LBF / 222.4N MIN.
OPERATING TEMP RANGE:	-40°F (-40°C) TO 257°F (125°C)
WEIGHT:	1.7 GRAMS EACH
BUNDLE DIAMETER:	$\varnothing 1/4"$ (6.35MM) TO $\varnothing 1-3/4"$ (44.5MM)
INSTALLATION TOOL:	12001 - HAND TOOL 12500 - PNEUMATIC TOOL
TOOL TENSION SETTING:	6 - 8
PACKAGING:	1000/BAG, 5 BAGS/MASTER

### **APPROVALS:**

ENG. APPR. *[Signature]* 2 Nov 12  
Q.A. APPR. *[Signature]* 11/02/12

SPECIFIED TOLERANCES  
INCHES (MM)  
.XX  $\pm$  .03 .X  $\pm$  .7  
.XXX  $\pm$  .01 .XX  $\pm$  .25  
ANGULAR:  $\pm 2^\circ$

MATERIAL  
**IMPACT MODIFIED  
HEAT STABILIZED NYLON 6/6**  
COLOR  
**BLACK**



**AVERY  
DENNISON**

FASTENER DIVISION  
FITCHBURG, MA 01420 U.S.A.  
TEL. 1-800-225-5913  
FAX. 978-353-8157

DESCRIPTION  
**M6 MOUNT TIE**  
STOCK NO. **20045-0**

REV.  
**C**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[20045-0](#)